

## Standard Pulp Disintegrator

Model No. 2532

This machine disintegrates the pulp into single fibers. by rotating the pulp with water at a high speed. This disintegration method is specified by JIS and ISO. Its applicable range is wide: paper sheet making, preparation of specimen for measurement of freeness, beating, bleaching, and screening.

### Specifications

<b>Capacity:</b>	2 liters
<b>Concentration:</b>	1.2%
<b>Specimen:</b>	24g (O.D.)
<b>Rotation Speed:</b>	3,000 rpm
<b>Timer:</b>	Automatic stop
<b>Referential Standards:</b>	JIS P-8220-1998, TAPPI T205om-88, ISO 5263
<b>Motor:</b>	100/110VAC 0.2kW 50/60Hz 6A
<b>Outer Dimensions:</b>	260 x 500 x 460mm
<b>Instrument Weight:</b>	30kg (tank weight 3.6kg)



Sold & serviced by:

**OpTest Equipment Inc.**

[www.optest.com](http://www.optest.com) - [sales@optest.com](mailto:sales@optest.com) - +1-613-632-5169